



# MASTER TL5 High Output

## MASTER TL5 HO 49W/865 1SL/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Colour designation	
Cap base	G5 [ G5]		Cool Daylight
Life to 50% failures preheat (nom.)	30000 h	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	92 lm/W
Features	na [ Not Applicable]	Correlated Colour Temperature (Nom)	6500 K
System description	High Output (HO)	Luminous efficacy (rated) (nom.)	83 lm/W
LSF preheat 2,000 hours rated	99 %	Color rendering index (max.)	85
LSF preheat 4,000 hours rated	99 %	Colour-rendering index (min.)	80
LSF preheat 6,000 hours rated	99 %	Colour rendering index (nom.)	82
LSF preheat 8,000 hours rated	99 %	LLMF 2000 h Rated	96 %
LSF preheat 16,000 hours rated	97 %	LLMF 4000 h Rated	95 %
LSF preheat 20,000 hours rated	84 %	LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical			
Colour Code	865 [ CCT of 6,500 K]		
Luminous flux (nom.)	4550 lm		
Luminous flux (rated) (nom.)	4075 lm		

# MASTER TL5 High Output

Operating and Electrical	
Power (Rated) (Nom)	49.2 W
Lamp current (nom.)	0.255 A
Temperature	
Design temperature (nom.)	35 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	Green Plate
Approval and Application	
Energy efficiency label (EEL)	A+

Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	54 kWh
Product Data	
Full product code	871150064389655
Order product name	MASTER TL5 HO 49W/865 SLV/40
EAN/UPC – product	8711500643896
Order code	64389655
SAP numerator – quantity per pack	1
Numerator – packs per outer box	40
SAP material	927927586555
SAP net weight (piece)	127.400 g
ILCOS code	FDH-49/65/1B-L/P-G5-16/1450


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 49W/865 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

## TL5 HO 49W/865

## Photometric data





LDPB\_TL5-HO8\_865-Spectral power distribution B/W



Lightcolour /865


# MASTER TL5 High Output

## Lifetime



LDLE\_TL5-HO8\_0001-Life expectancy diagram

LDLE\_TL5-HO8\_0002-Life expectancy diagram



LDLM\_TL5-HO8\_0001-Lumen maintenance diagram

