



MASTER TL5 High Output

MASTER TL5 HO 24W/830 UNP/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap base	G5 [G5]
Features	na [Not Applicable]
Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	1,950 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	76 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	22.5 W
Lamp current (nom.)	0.295 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	25 kWh
Product Data	
Order product name	MASTER TL5 HO 24W/830 UNP/40
Full product name	MASTER TL5 HO 24W/830 UNP/40
Full EOC	871150063698055
Order code	63698055
Material no. (12 NC)	927928083018
Local order code	24830IP
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500636980
Numerator – packs per outer box	40
EAN/UPC – Case	8711500636997


MASTER TL5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/830 UNP/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 24W/830 UNP/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 24W/830 UNP/40



Life Expectancy Diagram - MASTER TL5 HO 24W/830 UNP/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 24W/830 UNP/40

