



Eco passport

MASTER TL5 High Output

MASTER TL5 HO 24W/830 1SL/40



Энергия

- Power (Rated) (Nom) : 22.5 W
- Luminous Efficacy (@ Max Lumen, Rated) (Nom) : 87 lm/W
- Luminous Efficacy (rated) (Nom) : 76 lm/W
- Energy Efficiency Label : A
- Dimmable : Yes



Материали

- Mercury (Hg) Content (Nom) : 1.4 mg



ЖИВОТ

- Life to 50% Failures Preheat (Nom) : 30000 h