



# MASTER TL5 High Output



## MASTER TL5 HO 24W/840 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G5
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	1,700 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	76 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	22.7 W
Lamp current (nom.)	0.295 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	23 kWh
EPREL registration number	423555
Product Data	
Order product name	MASTER TL5 HO 24W/840 SLV/40
Full product name	MASTER TL5 HO 24W/840 1SL/40
Full EOC	871150063960855
Order code	63960855
Material no. (12 NC)	927928084055
SAP numerator – quantity per pack	1

# MASTER TL5 High Output


EAN/UPC — Product/Case	8711500639608
Numerator – packs per outer box	40
EAN/UPC - Case	8711500867841

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/840 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 24W/840 SLV/40

## Lifetime



Life Expectancy Diagram - MASTER TL5 HO 24W/840 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 24W/840 SLV/40

# MASTER TL5 High Output

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 24W/840 SLV/40

