

PHILIPS

Lighting



MASTER TL5 High Output 高亮度日光燈管

MASTER TL5 HO 24W/865 SLV/40

直徑 16 mm 的螢光燈管

产品数据

基本資訊	
接口	G5 [G5]
至 50% 故障預熱的使用時間 (標稱)	30000 h
功能	na [Not Applicable]
系統說明	高輸出 (HO)
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	99 %
額定 LSF (預熱 8000 小時), 3 小時	99 %
額定 LSF (8000 小時), 3 小時	99 %
額定 LSF (預熱 16000 小時), 3 小時	97 %
額定 LSF (預熱 2000 小時), 3 小時	84 %

照明科技	
色碼	865 [CCT of 6500K]
光通量 (標稱)	1825 lm
光通量 (額定) (標稱)	1575 lm
色彩名稱	冷日光
光效 (於最大流明, 額定) (標稱)	81 lm/W
相關色溫 (標稱)	6500 K
光效 (額定) (標稱)	72 lm/W
演色性指數 (最大)	85
演色性指數 (最小)	80
演色性指數 (標稱)	82

額定 SLMF (2000 小時)	96 %
額定 SLMF (4000 小時)	95 %
額定 SLMF (6000 小時)	94 %
額定 SLMF (8000 小時)	93 %
額定 SLMF (12000 小時)	92 %
額定 SLMF (16000 小時)	91 %
額定 SLMF (20000 小時)	90 %

運作和電氣	
Power (Rated) (Nom)	22.5 W
燈具電流 (標稱)	0.295 A

溫度	
設計溫度 (標稱)	35 °C

控制調光	
可調光	Yes

機械和殼體	
接口資訊	綠色底座

應用	
能源效益標籤 (EEL)	A

MASTER TL5 High Output 高亮度日光燈管


汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	25 kWh
產品參數	
完整產品碼	871150064393355
訂購產品名稱	MASTER TL5 HO 24W/865 SLV/40
EAN/UPC - 產品	8711500643933
訂購代碼	927928086555

分子 - 各件數量	1
分子 - 每一外盒內件數	40
材質編號(I2NC)	927928086555
淨重 (件)	52.000 g
ILCOS Code	FDH-24/65/1B-L/P-G5-16/550

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


二维绘图




TL5 HO 24W/865

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/865 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

光度数据




LDPB_TL5-HO8_865-Spectral power distribution B/W




LDPO_TL5-HO8_865-Spectral power distribution Colour

MASTER TL5 High Output 高亮度日光燈管

壽命



LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

