



MASTER TL5 High Output



MASTER TL5 HO 39W/865 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G5	Dimmable	Yes
Features	na [Not Applicable]		
Flux measurement reference	Sphere		
Light Technical		Mechanical and Housing	
Color Code	865 [CCT of 6500K]	Bulb Shape	T5
Luminous Flux	2.875 lm		
Color Designation	Cool Daylight		
Chromaticity Coordinate X (Nom)	0.313		
Chromaticity Coordinate Y (Nom)	0.337		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	76 lm/W		
Color rendering index (CRI)	82		
Operating and Electrical		Approval and Application	
Power Consumption	38.0 W	Energy Efficiency Class	G
Lamp Current (Nom)	0.325 A	Mercury (Hg) Content (Nom)	1.2 mg
		Energy Consumption kWh/1000 h	38 kWh
		EPREL Registration Number	423560
Product Data			
Order product name	MASTER TL5 HO 39W/865 SLV/40		
Full product name	MASTER TL5 HO 39W/865 1SL/40		
Full product code	871150064387255		
Order code	64387255		
Material Nr. (12NC)	927928586555		
Numerator - Quantity Per Pack	1		

MASTER TL5 High Output


EAN/UPC - Product/Case	8711500643872
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500868503

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 39W/865 SLV/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 39W/865 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 39W/865 SLV/40



Lumen Maintenance Diagram - MASTER TL5 HO 39W/865 SLV/40

MASTER TL5 High Output

Lifetime

Life Expectancy Diagram - MASTER TL5 HO 39W/865 SLV/40

