



MASTER TL5 High Output

MASTER TL5 HO 54W/840 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	G5	Dimmable	Yes
Features	na [Not Applicable]		
Flux measurement reference	Sphere		
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T5
Luminous Flux	4,500 lm		
Color Designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	1.2 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	55 kWh
Luminous Efficacy (rated) (Nom)	83 lm/W	EPREL Registration Number	423564
Color rendering index (CRI)	80		
Operating and Electrical		Product Data	
Power Consumption	54.4 W	Order product name	MASTER TL5 HO 54W/840 SLV/40
Lamp Current (Nom)	0.455 A	Full product name	MASTER TL5 HO 54W/840 SLV/40
		Full product code	871150064318655
		Local code description	TL554W840HO
		Order code	927929084055
		Material Nr. (12NC)	927929084055

MASTER TL5 High Output

Local order code	TL554W840HO
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500643186
Numerator - Packs per outer box	40


EAN/UPC - Case	8711500868831
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/840 SLV/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 54W/840 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 54W/840 SLV/40



Lumen Maintenance Diagram - MASTER TL5 HO 54W/840 SLV/40

MASTER TL5 High Output

Lifetime

Life Expectancy Diagram - MASTER TL5 HO 54W/840 SLV/40

