



MASTER TL5 High Output

MASTER TL5 HO 54W/850 UNP/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5 [G5]
Features	na [Not Applicable]
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	4,800 lumen
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	54.1 W
Lamp Current (Nom)	0.455 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	59 kWh
Product Data	
Full product code	871150063743755
Order product name	MASTER TL5 HO 54W/850 UNP/40
Order code	927929085018
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40

MASTER TL5 High Output


Material Nr. (12NC)	927929085018
Full product name	MASTER TL5 HO 54W/850 UNP/40
EAN/UPC - Case	8711500637444

EAN/UPC - Product/Case	8711500637437
------------------------	---------------

Dimensional drawing


Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/850 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HO 54W/850 UNP/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HO 54W/850 UNP/40

Life Expectancy Diagram - MASTER TL5 HO 54W/850 UNP/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 54W/850 UNP/40

