



# MASTER TL5 High Output

## MASTER TL5 HO 54W/865 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Product data

General Information		LLMF 2000 h Rated		96 %	
Cap base	G5 [ G5]	LLMF 4000 h Rated	95 %		
Life to 50% failures preheat (nom.)	30000 h	LLMF 6000 h Rated	94 %		
Features	na [ Not Applicable]	LLMF 8000 h Rated	93 %		
System description	High Output (HO)	LLMF 12000 h Rated	92 %		
LSF Preheat 2000 h Rated	99 %	LLMF 16000 h Rated	91 %		
LSF Preheat 4000 h Rated	99 %	LLMF 20000 h Rated	90 %		
LSF Preheat 6000 h Rated	99 %	<b>Operating and Electrical</b>			
LSF Preheat 8000 h Rated	99 %	Power (Rated) (Nom)	54.1 W		
LSF Preheat 16000 h Rated	97 %	Lamp current (nom.)	0.455 A		
LSF Preheat 20000 h Rated	84 %	<b>Temperature</b>			
<b>Light Technical</b>		Design temperature (nom.)	35 °C		
Colour code	865 [ CCT of 6,500 K]	<b>Controls and Dimming</b>			
Luminous flux (nom.)	4650 lm	Dimmable	yes		
Luminous flux (rated) (nom.)	4200 lm	<b>Mechanical and Housing</b>			
Colour designation	Cool Daylight	Cap base information	Green Plate		
Luminous efficacy (@ max. lumen, rated) (nom.)	86 lm/W	<b>Approval and Application</b>			
Correlated colour temperature (nom.)	6500 K	Energy efficiency label (EEL)	A		
Luminous efficacy (rated) (nom.)	78 lm/W				
Color rendering index (max.)	85				
Color rendering index (min.)	80				
Color rendering index (nom.)	85				

# MASTER TL5 High Output


Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	59 kWh
<b>Product Data</b>	
Full product code	871150064391955
Order product name	MASTER TL5 HO 54W/865 SLV/40
EAN/UPC – product	8711500643919
Order code	64391955

Local Code	54865
Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927929086555
Net weight (piece)	105.800 g
ILCOS Code	FDH-54/65/1B-L/P-G5-16/1150

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/865 SLV/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

## TL5 HO 54W/865

## Photometric data



## Lightcolour /865



## Lightcolour /865

# MASTER TL5 High Output

## Lifetime

