



MASTER TL5 High Output



MASTER TL5 HO 54W/865 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information			
Cap-Base	G5 [G5]	Luminous Flux (Rated) (Nom)	4200 lm
Life to 50% Failures Preheat (Nom)	30000 h	Color Designation	Cool Daylight
Features	na [Not Applicable]	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	86 lm/W
System Description	High Output	Chromaticity Coordinate X (Nom)	0.313
LSF Preheat 2000 h Rated	99 %	Chromaticity Coordinate Y (Nom)	0.337
LSF Preheat 4000 h Rated	99 %	Correlated Color Temperature (Nom)	6500 K
LSF Preheat 6000 h Rated	99 %	Luminous Efficacy (rated) (Nom)	78 lm/W
LSF Preheat 8000 h Rated	99 %	Color Rendering Index (Max)	85
LSF Preheat 16000 h Rated	97 %	Color Rendering Index (Min)	80
LSF Preheat 20000 h Rated	84 %	Color Rendering Index (Nom)	82
Flux measurement reference	Sphere	LLMF 2000 h Rated	96 %
		LLMF 4000 h Rated	95 %
		LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
Light technical			
Color Code	865 [CCT of 6500K]		
Luminous Flux (Nom)	4200 lm		

MASTER TL5 High Output

LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and electrical

Power (Nom)	54.4 W
Lamp Current (Nom)	0.455 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and dimming

Dimmable	Yes
----------	-----

Mechanical and housing

Cap-Base Information	Green Plate
Bulb Shape	T5 [16 mm (T5)]

Approval and application


Energy Efficiency Class	G
-------------------------	---

Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	55 kWh
EPREL Registration Number	423565

Product data

Full product code	871150064391955
Order product name	MASTER TL5 HO 54W/865 SLV/40
EAN/UPC - Product	8711500643919
Order code	927929086555
Numerator - Quantity Per Pack	1
Local code description	LAMP. FLUOR. TUB. TL5-54WHO/ 865SL
Numerator - Packs per outer box	40
Material Nr. (12NC)	927929086555
Net Weight (Piece)	105.800 g
ILCOS Code	FDH-54/65/1B-L/P-G5-16/1150


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/865 SLV/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

MASTER TL5 HO 54W/865 SLV/40

Photometric data



LDPB_TL5-HO8_865-Spectral power distribution B/W



LDPO_TL5-HO8_865-Spectral power distribution Colour

MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

