



# TL5 Essential HO Super 80

## TL5 Essential HO 54W/830 1SL/40

Low-pressure mercury discharge T5 lamp with tubular 16 mm envelope and high lumen output.

### Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3-hour cycle) with ENEC-compliant preheat ballast Lifetime performance may differ on non-ENEC-compliant ballasts


### Product data

General Information	
Cap-Base	G5 [G5]
Features	HO [High Output]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	5,000 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	54 W
Lamp Current (Nom)	0.460 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	54 kWh
Product Data	
Order product name	TL5 Essential HO 54W/830 1SL/40
Full product name	TL5 Essential HO 54W/830 1SL/40
Full product code	871829118274000
Order code	927929383040
Material Nr. (12NC)	927929383040
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291182740
Numerator - Packs per outer box	40
EAN/UPC - Case	8718291182757


# TL5 Essential HO Super 80

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential HO 54W/830	17.0 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
1SL/40					

## Photometric data



Spectral Power Distribution Colour - TL5 Essential HO 54W/830 1SL/40

