



MASTER TL5 High Output

MASTER TL5 HO 80W/830 1SL/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	G5 [G5]	Power Consumption	79.8 W
Features	na [Not Applicable]	Lamp Current (Nom)	0.530 A
Flux measurement reference	Sphere		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	6,550 lumen		
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.44	Bulb Shape	T5 [16 mm (T5)]
Chromaticity Coordinate Y (Nom)	0.403		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	82 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	81	Mercury (Hg) Content (Nom)	1.2 mg
		Energy Consumption kWh/1000 h	80 kWh
		EPREL Registration Number	423569


MASTER TL5 High Output

Product Data

Full product code	871150071040655
Order product name	MASTER TL5 HO 80W/830 SLV/40
Order code	71040655
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40


Material Nr. (12NC)	927929583057
Full product name	MASTER TL5 HO 80W/830 1SL/40
EAN/UPC - Case	8711500868855
EAN/UPC - Product/Case	8711500710406

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 80W/830 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HO 80W/830 SLV/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HO 80W/830 SLV/40

Life Expectancy Diagram - MASTER TL5 HO 80W/830 SLV/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 80W/830 SLV/40

