



MASTER PL-L Polar 4 Pin

MASTER PL-L POLAR 36W/840/4P 1CT/25

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 2 parallel fluorescent tubes linked by a bridge 4-pin base without gear

Product data

General Information	
Cap base	2G11 [2G11]
Main application	Low Temperature [Low Temperature environment]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h
System description	na [-]
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	94 %
LSF 12000 h Rated	80 %
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %

Light Technical	
Colour code	840 [CCT of 4,000 K]
Luminous flux (nom.)	2900 lm
Luminous flux (rated) (nom.)	2900 lm
Colour designation	Cool White (CW)
Correlated colour temperature (nom.)	4000 K
Luminous efficacy (rated) (nom.)	81 lm/W
Color rendering index (nom.)	82
LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	93 %
LLMF 6000 h Rated	92 %
LLMF 8000 h Rated	91 %
LLMF 12000 h Rated	90 %
LLMF 16000 h Rated	90 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Rated) (Nom)	36.0 W
Lamp current (nom.)	0.445 A

MASTER PL-L Polar 4 Pin


Temperature	
Design temperature (nom.)	18 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg
Energy Consumption kWh/1000 h	40 kWh

Product Data	
Full product code	871150026160140
Order product name	MASTER PL-L Polar 36W/840/4P 1CT/25
EAN/UPC – product	8711500261601
Order code	26160140
Local Code	36PLL840POLAR
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927931084070
Net weight (piece)	104.000 g
ILCOS Code	FSD-36/40/1B-E-2G11

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing





PL-L 36W/840/4P LT

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L Polar 36W/ 840/4P 1CT/25	39.0 mm	18.0 mm	385 mm	410 mm	416.6 mm

MASTER PL-L Polar 4 Pin

Photometric data



Lightcolour /840

Lightcolour /840

