



# MASTER PL-L Polar 4 Pin



## MASTER PL-L POLAR 55W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes linked by a bridge. 4-pin base without gear

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap base	2G11	Power Consumption	55.3 W
Flux measurement reference	Sphere	Lamp current (nom.)	0.550 A
Light Technical		Controls and Dimming	
Colour Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	4,650 lm	Approval and Application	
Colour designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) content (max.)	2 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) content (nom.)	2.0 mg
Correlated Colour Temperature	4000 K	Energy consumption kWh/1,000 hours	56 kWh
Luminous efficacy (rated) (nom.)	87 lm/W	EPREL registration number	423577
Colour rendering index (CRI)	80		

MASTER PL-L Polar 4 Pin

Product Data	
Order product name	MASTER PL-L Polar 55W/840/4P 1CT/25
Full product name	MASTER PL-L POLAR 55W/840/4P 1CT/25
Full EOC	871150026164940
Order code	26164940
Material no. (12 NC)	927931584070
Local order code	55PLL840POLAR


SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500261649
Numerator – packs per outer box	25
EAN/UPC – Case	8711500261656

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L Polar 55W/840/4P 1CT/25	39.0 mm	18.0 mm	510 mm	535 mm	541.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L Polar 55W/840/4P 1CT/25

