



# PL-T Triple 4-Pin Base Non Amalgam

## PL-T 42W/830/4P/ALTO

Philips Non-Amalgam PL-T Compact Fluorescent lamps offer designers, specifiers, and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities.


### Product data

General Information	
Cap-Base	GX24Q-4 [GX24q-4]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	3,000 lumen
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (Rated) (Min)	73.2 lm/W
Luminous Efficacy (rated) (Nom)	70.7 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	41.0 W
Lamp Current (Nom)	0.320 A
Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	45 kWh
Product Data	
Order product name	PL-T 42W/830/4P/ALTO
Order code	927933283030
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927933283030
Full product name	PL-T 42W/830/4P/ALTO
EAN/UPC - Case	50046677433463
EAN/UPC - Product/Case	046677433468


# PL-T Triple 4-Pin Base Non Amalgam

## Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 42W/830/4P/ALTO	41.0 mm	120.7 mm	145.0 mm	160.7 mm

## Photometric data




Spectral Power Distribution Colour - PL-T 42W/830/4P/ALTO

## Lifetime




Life Expectancy Diagram - PL-T 42W/830/4P/ALTO



Life Expectancy Diagram - PL-T 42W/830/4P/ALTO

## PL-T Triple 4-Pin Base Non Amalgam

### Lifetime



Lumen Maintenance Diagram - PL-T 42W/830/4P/ALTO

