

MASTER PL-S 2 Pin

MASTER PL-S 7W/840/2P 1CT/5X10BOX

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General information			
Cap base	G23 [G23]	Luminous flux (nom.)	400 lm
Life to 10% failures (nom.)	6500 h	Luminous flux (rated) (nom.)	405 lm
Life to 50% failures (nom.)	10000 h	Colour designation	Cool White (CW)
LSF 2000 h Rated	99 %	Chromaticity coordinate X (nom.)	0.38
LSF 4000 h Rated	98 %	Chromaticity coordinate Y (nom.)	0.38
LSF 6000 h Rated	95 %	Correlated Colour Temperature (Nom)	4000 K
LSF 8000 h Rated	86 %	Luminous efficacy (rated) (nom.)	57 lm/W
	Sphere	Colour rendering index (nom.)	80
		LLMF 2000 h Rated	94 %
		LLMF 4000 h Rated	91 %
		LLMF 6000 h Rated	89 %
Light technical			
Colour Code	841 [CCT of 4100K (841)]		

MASTER PL-S 2 Pin

LLMF 8000 h Rated	86 %
Operating and electrical	
Power (Rated) (Nom)	7.2 W
Lamp current (nom.)	0.175 A
Temperature	
Design temperature (nom.)	28 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Cap-base information	2P
Approval and application	
Energy Efficiency Class	G

Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	8 kWh
	423585
Product data	
Full product code	871150026065970
Order product name	MASTER PL-S 7W/840/2P 1CT/5X10BOX
EAN/UPC – product	8711500260659
Order code	26065970
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	927935684011
Copy Net Weight (Piece)	26.000 g
ILCOS code	FSD-7/40/1B-I-G23


Dimensional drawing



MASTER PL-S 7W/840/2P 1CT/5X10BOX

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 7W/840/2P 1CT/5X10BOX	28 mm	13 mm	97 mm	113 mm	135 mm

Photometric data



LDPB_PLS2PLM_840-Spectral power distribution B/W

Lightcolour /840

MASTER PL-S 2 Pin

Lifetime



LDLE_PLS2PLM_0002-Life expectancy diagram

LDLE_PLS2PLM_0001-Life expectancy diagram



LDLM_PLS2PLM_0001-Lumen maintenance diagram

