



MASTER PL-S 2 Pin

MASTER PL-S 11W/865/2P 1CT/10

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G23	Power Consumption	11.6 W
Life to 50% Failures (Nom)	10,000 hour(s)	Lamp Current (Nom)	0.160 A
Light Technical		Voltage (Nom)	89 V
Color Code	865 [CCT of 6500K]	Voltage (Nom)	89 V
Luminous Flux	835 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	70 lm/W	Mercury (Hg) Content (Nom)	1.4 mg
Color rendering index (CRI)	82		

MASTER PL-S 2 Pin

Product Data	
Order product name	MASTER PL-S 11W/865/2P 1CT/10
Full product name	MASTER PL-S 11W/865/2P 1CT/10
Full product code	871869960710400
Order code	927936486565
Material Nr. (12NC)	927936486565


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699607104
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699607111

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 11W/865/2P 1CT/10	28 mm	13 mm	97 mm	113 mm	135 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-S 11W/865/2P 1CT/10

Lifetime




Life Expectancy Diagram - MASTER PL-S 11W/865/2P 1CT/10



Life Expectancy Diagram - MASTER PL-S 11W/865/2P 1CT/10

MASTER PL-S 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-S 11W/865/2P 1CT/10

