



# PL-Q 4 Pin

## PL-Q 16W/835/4P 1CT/10BOX

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 4-pin version is designed for operation on electronic gear.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	GR10Q [ GR10q]
Life to 50% failures preheat (nom.)	13000 h
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	98 %
LSF preheat 6,000 hours rated	95 %
LSF preheat 8,000 hours rated	89 %
LSF preheat 16,000 hours rated	22 %
LSF preheat 20,000 hours rated	4 %
Light Technical	
Colour Code	835 [ CCT of 3,500 K]
Luminous flux (nom.)	1050 lm
Luminous flux (rated) (nom.)	1050 lm


Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3500 K
Luminous efficacy (rated) (nom.)	66.6 lm/W
Colour rendering index (nom.)	82
LLMF 2000 h Rated	90 %
LLMF 4000 h Rated	86 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	80 %
LLMF 12000 h Rated	79 %
LLMF 16000 h Rated	78 %
LLMF 20000 h Rated	78 %
Operating and Electrical	
Power (Rated) (Nom)	16.0 W

## PL-Q 4 Pin

Lamp current (nom.)	0.195 A
<b>Temperature</b>	
Design temperature (nom.)	25 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
<b>Mechanical and Housing</b>	
Cap-base information	4P
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4 mg

Energy consumption kWh/1,000 hours	18 kWh
<b>Product Data</b>	
Full product code	871150027206525
Order product name	PL-Q 16W/835/4P 1CT/10BOX
EAN/UPC – product	8711500272065
Order code	27206525
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	927939183540
SAP net weight (piece)	68.000 g
ILCOS code	FSS-16/35/1B-E-GR10q

### Dimensional drawing




PL-Q 16W/835/4P

Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 16W/ 835/4P 1CT/ 10BOX	40 mm	13.7 mm	27.5 mm	138 mm	49 mm	40.5 mm	135 mm

### Photometric data

''



LDPB\_PLQ4P\_835-Spectral power distribution B/W

Lightcolour /835


# PL-Q 4 Pin

## Lifetime



LDLM\_PLQ4P\_0001-Lumen maintenance diagram

LDLE\_PLQ4P\_0002-Life expectancy diagram



LDLE\_PLQ4P\_0001-Life expectancy diagram

