



PL-Q 4 Pin



PL-Q 38W/840/4P 1CT/10BOX

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 4-pin version is designed for operation on electronic gear.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	GR10q	Power Consumption	38.4 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.430 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	2,750 lm	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) Content (Max)	3 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	4 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	39 kWh
Luminous Efficacy (rated) (Nom)	75 lm/W	EPREL Registration Number	423617
Color rendering index (CRI)	81		

PL-Q 4 Pin

Product Data	
Order product name	PL-Q 38W/840/4P 1CT/10BOX
Full product name	PL-Q 38W/840/4P 1CT/10BOX
Full product code	871150027174725
Order code	927939484040
Material Nr. (12NC)	927939484040


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500271747
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500271662

Dimensional drawing




Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 38W/840/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm

Photometric data




Spectral Power Distribution Colour - PL-Q 38W/840/4P 1CT/10BOX

Lifetime




Lumen Maintenance Diagram - PL-Q 38W/840/4P 1CT/10BOX



Life Expectancy Diagram - PL-Q 38W/840/4P 1CT/10BOX

PL-Q 4 Pin

Lifetime



Life Expectancy Diagram - PL-Q 38W/840/4P 1CT/10BOX

