



MASTER TL5 Circular

MASTER TL5 Circular 22W/840 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	2GX13	0.300 A	
Nominal lifetime	12,000 hour(s)	Controls and Dimming	
Flux measurement reference	Sphere	Dimmable	
Light Technical		Yes	
Color Code	840 [CCT of 4000K]	Mechanical and Housing	
Luminous Flux	1,800 lm	Bulb Shape	
Color Designation	Cool White (CW)	C-T5	
Chromaticity Coordinate X (Nom)	0.38	Approval and Application	
Chromaticity Coordinate Y (Nom)	0.38	Energy Efficiency Class	
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Max)	
Luminous Efficacy (rated) (Nom)	82 lm/W	Mercury (Hg) Content (Nom)	
Color rendering index (CRI)	81	Energy Consumption kWh/1000 h	
Operating and Electrical		EPREL Registration Number	
Power Consumption	23.5 W	Product Data	
		Order product name	
		MASTER TL5 Circular 22W/840 1CT/10	

MASTER TL5 Circular

Full product name	MASTER TL5 Circular 22W/840 1CT/10
Full product code	871150064221925
Order code	927965084013
Material Nr. (12NC)	927965084013
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500642219
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500642226

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 22W/840 1CT/10	18 mm	14 mm	220 mm	230 mm	187 mm	197 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 22W/840 1CT/10

Lifetime



Life Expectancy Diagram - MASTER TL5 Circular 22W/840 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 22W/840 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 22W/840 1CT/10

