



MASTER TL5 Circular

MASTER TL5 Circular 22W/840 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2GX13 [2GX13]
Nominal lifetime	12,000 hour(s)
Flux measurement reference	Sphere
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,800 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color rendering index (CRI)	81
Operating and Electrical	
Power Consumption	23.5 W


Lamp Current (Nom)	0.300 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T5 [C-T5 16 mm]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	4 mg
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	24 kWh
EPREL Registration Number	423619
Product Data	
Order product name	MASTER TL5 Circular 22W/840 1CT/10

MASTER TL5 Circular

Full product name	MASTER TL5 Circular 22W/840 1CT/10
Full product code	871150064221925
Order code	927965084013
Material Nr. (12NC)	927965084013
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500642219
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500642226

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 22W/840 1CT/10	18 mm	14 mm	220 mm	230 mm	187 mm	197 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 22W/840 1CT/10

Lifetime




Life Expectancy Diagram - MASTER TL5 Circular 22W/840 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 22W/840 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 22W/840 1CT/10

