



MASTER TL5 Circular

MASTER TL5 Circular 40W/865 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2GX13 [2GX13]
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	3,100 lumen
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	78 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	39.9 W
Lamp Current (Nom)	0.320 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T5 [C-T5 16 mm]
Approval and Application	
Mercury (Hg) Content (Nom)	2.5 mg
Product Data	
Full product code	871150027650600
Order product name	MASTER TL5 Circular 40W/865 1CT/10
Order code	927965586513
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927965586513
Full product name	MASTER TL5 Circular 40W/865 1CT/10


MASTER TL5 Circular

EAN/UPC - Case	8711500276469
EAN/UPC - Product/Case	8711500276506

Dimensional drawing


Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 40W/865 1CT/10	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 Circular 40W/865 1CT/10

Lifetime



Life Expectancy Diagram - MASTER TL5 Circular 40W/865 1CT/10

Life Expectancy Diagram - MASTER TL5 Circular 40W/865 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 40W/865 1CT/10

