



MASTER TL5 Circular



MASTER TL5 CIRCULAR 55W/830 1CT/10

16 mm tube diameter circular fluorescent lamps with a choice of various diameters

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap base	2GX13 [2GX13]
Nominal lifetime	12,000 h
Flux measurement reference	Sphere
Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	4,210 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	76 lm/W
Colour rendering index (CRI)	81
Operating and Electrical	
Power Consumption	55.7 W
Lamp current (nom.)	0.550 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	C-T5 [C-T5 16 mm]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	4 mg
Mercury (Hg) content (nom.)	4 mg
Energy consumption kWh/1,000 hours	56 kWh
EPREL registration number	423622
Product Data	
Order product name	MASTER TL5 Circular 55W/830 1CT/10
Full product name	MASTER TL5 CIRCULAR 55W/830 1CT/10
Full EOC	871150064279025
Order code	64279025
Material no. (12 NC)	927965783013
Local order code	55TL5C830
SAP numerator – quantity per pack	1

MASTER TL5 Circular


EAN/UPC — Product/Case	8711500642790
Numerator – packs per outer box	10
EAN/UPC - Case	8711500642806

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 55W/830 1CT/10	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 55W/830 1CT/10

Lifetime




Life Expectancy Diagram - MASTER TL5 Circular 55W/830 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 55W/830 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 55W/830 1CT/10

