



MASTER TL5 Circular

MASTER TL5 CIRCULAR 60W/840 1CT/10

16 mm tube diameter circular fluorescent lamps with a choice of various diameters

Product data

General Information	
Cap base	2GX13 [2GX13]
Life to 50% failures preheat (nom.)	12000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	96 %
LSF Preheat 8000 h Rated	89 %
LSF Preheat 16000 h Rated	10 %
LSF Preheat 20000 h Rated	1 %
Light Technical	
Colour code	840 [CCT of 4,000 K]
Luminous flux (nom.)	5000 lm
Luminous flux (rated) (nom.)	5000 lm
Colour designation	Cool White (CW)
Correlated colour temperature (nom.)	4000 K
Luminous efficacy (rated) (nom.)	83 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	85
LLMF 2000 h Rated	91 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	84 %
LLMF 8000 h Rated	81 %
LLMF 12000 h Rated	77 %
LLMF 16000 h Rated	74 %

LLMF 20000 h Rated	72 %
Operating and Electrical	
Power (Rated) (Nom)	60.0 W
Lamp current (nom.)	0.470 A
Temperature	
Design temperature (nom.)	35 °C
Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.5 mg
Energy Consumption kWh/1000 h	66 kWh
Product Data	
Full product code	871150064261525
Order product name	MASTER TL5 Circular 60W/840 1CT/10
EAN/UPC – product	8711500642615
Order code	64261525
Local Code	60TL5C840
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (I2NC)	927966084013


MASTER TL5 Circular

Net weight (piece)	145.000 g
ILCOS Code	FSCH-60/40/1B-L/P-2GX13-16

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL5-C 60W/840

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 60W/840 1CT/10	18 mm	14 mm	367 mm	379 mm	334 mm	346 mm

Photometric data



Lightcolour /840



Lightcolour /840

MASTER TL5 Circular

Lifetime

