



# MASTER TL5 Circular

## MASTER TL5 Circular 60W/840 1CT/10

16 mm tube diameter circular fluorescent lamps with a choice of various diameters

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | 2GX13 [2GX13]      |
| Flux measurement reference         | Sphere             |
| Light Technical                    |                    |
| Color Code                         | 840 [CCT of 4000K] |
| Luminous Flux                      | 5,000 lm           |
| Color Designation                  | Cool White (CW)    |
| Chromaticity Coordinate X (Nom)    | 0.38               |
| Chromaticity Coordinate Y (Nom)    | 0.38               |
| Correlated Color Temperature (Nom) | 4000 K             |
| Luminous Efficacy (rated) (Nom)    | 83 lm/W            |
| Color rendering index (CRI)        | 81                 |
| Operating and Electrical           |                    |
| Power Consumption                  | 60.6 W             |
| Lamp Current (Nom)                 | 0.470 A            |


| Controls and Dimming          |                                    |
|-------------------------------|------------------------------------|
| Dimmable                      | Yes                                |
| Mechanical and Housing        |                                    |
| Bulb Shape                    | C-T5 [C-T5 16 mm]                  |
| Approval and Application      |                                    |
| Energy Efficiency Class       | G                                  |
| Mercury (Hg) Content (Max)    | 4 mg                               |
| Mercury (Hg) Content (Nom)    | 4 mg                               |
| Energy Consumption kWh/1000 h | 61 kWh                             |
| EPREL Registration Number     | 423625                             |
| Product Data                  |                                    |
| Order product name            | MASTER TL5 Circular 60W/840 1CT/10 |
| Full product name             | MASTER TL5 Circular 60W/840 1CT/10 |
| Full product code             | 871150064261525                    |
| Order code                    | 927966084013                       |

MASTER TL5 Circular

|                                 |               |
|---------------------------------|---------------|
| Material Nr. (12NC)             | 927966084013  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8711500642615 |
| Numerator - Packs per outer box | 10            |


|                |               |
|----------------|---------------|
| EAN/UPC - Case | 8711500642622 |
|----------------|---------------|

Dimensional drawing




| Product                            | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|------------------------------------|---------|---------|---------|---------|---------|---------|
| MASTER TL5 Circular 60W/840 1CT/10 | 18 mm   | 14 mm   | 367 mm  | 379 mm  | 334 mm  | 346 mm  |

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 60W/840 1CT/10

Lifetime



Life Expectancy Diagram - MASTER TL5 Circular 60W/840 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 60W/840 1CT/10

# MASTER TL5 Circular

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 60W/840 1CT/10

