



MASTER TL-D Super 80

TL-D 18W/865 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h
Life to 50% failures preheat (nom.)	20000 h

Light Technical	
Colour Code	865 [CCT of 6,500 K]
Lamp Luminous Flux (Nom)	1275 lm
Colour Designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	96 %
Lumen maintenance 5,000 hours (nom.)	94 %
Colour Temperature, horizontal (Nom)	6500 K
Lamp Luminous Efficacy EM (Nom)	71 lm/W
Colour Rendering Index,horiz (Nom)	80

Operating and Electrical	
Power (Rated) (Nom)	18 W
Lamp current (nom.)	0.360 A
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	Green [Green Cap]

Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg


Product Data	
Full product code	871829125418800
Order product name	TL-D 18W/865 1SL/25
EAN/UPC – product	8718291254188
Order code	927981186524
Local Code	TLD18W865ALTO
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927981186524
Net weight (piece)	0.070 kg

MASTER TL-D Super 80

Warnings and Safety



- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing





Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/865 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Lifetime



MASTER TL-D Super 80

Lifetime

