



TL-D LIFEMAX Super 80

TL-D 36W/840 1SL/25

A lâmpada TL-D LIFEMAX Super 80 oferece mais lúmens por watt e melhor reprodução de cores do que as lâmpadas padrão TL-D. Além disso, tem um menor teor de mercúrio. A lâmpada pode ser aplicada em luminárias TL-D existentes.

Dados do produto

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life To 50% Failures (Nom)	15000 h
Life To 50% Failures Preheat (Nom)	20000 h

Light Technical	
Color Code	840 [TCC de 4000K (841)]
Luminous Flux (Rated) (Nom)	3250 lm
Color Designation	Branca fria (CW)
Manutenção lumínica 2000h (Nom.)	96 %
Manutenção lumínica a 5000 h (Nom)	94 %
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Índice de restituição cromática (Nom.)	82

Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp Current (Nom)	0,440 A
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	Sim

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2,0 mg

Product Data	
Full product code	871150028561441
Order product name	TL-D 36W/840 1SL/25
EAN/UPC - Product	8711500285614
Order code	927982284040
Local Code	TLD36W-840-ECO
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927982284040
Net Weight (Piece)	134,400 g

TL-D LIFEMAX Super 80




Desenho dimensional



TL-D 36W/840 CW G13

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/840 1SL/25	28 mm	1199,4 mm	1206,5 mm	1204,1 mm	1213,6 mm

Vida útil



TL-D LIFEMAX Super 80

