



# MASTER TL-D Xtra Polar

## MASTER TL-D Xtra Polar 36W/840 T12 SLV

The MASTER TL-D Xtra Polar lamp offers the highest light output at lower temperatures because of the insulation that is created by putting a TL-D (T8) lamp into a T12 tube. The lamp is especially suitable for applications in cold environments where relamping is costly and complex.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	30000 h
Life to 50% Failures (Nom)	36000 h
Life to 50% Failures Preheat (Nom)	55000 h
LSF 2000 h Rated	100 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	99 %
LSF 16000 h Rated	99 %
LSF 20000 h Rated	99 %
Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	3350 lm
Luminous Flux (Rated) (Nom)	3350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	91 lm/W

Color Rendering Index (Nom)	85
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Rated) (Nom)	35.0 W
Lamp Current (Nom)	0.453 A

### Temperature

Design Temperature (Nom)	5 °C
--------------------------	------

### Controls and Dimming

Dimmable	Yes
----------	-----

# MASTER TL-D Xtra Polar

## Mechanical and Housing

Cap-Base Information Green Plate

## Approval and Application

Energy Efficiency Label (EEL) A  
 Mercury (Hg) Content (Nom) 3.0 mg  
 Energy Consumption kWh/1000 h 41 kWh

## Product Data


Full product code 871150089317825

Order product name	MASTER TL-D Xtra Polar 36W/840 T12 SLV
EAN/UPC - Product	8711500893178
Order code	927982684075
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927982684075
Net Weight (Piece)	398.000 g
ILCOS Code	FD-36/40/1B-E-G13

## Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra Polar 36W/840 T12 SLV	40.5 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

## TL-D Xtra Polar 36W/840 T12

## Photometric data





## Lightcolor /840

## Lightcolor /840



# MASTER TL-D Xtra Polar

## Lifetime



MASTER TL-D Xtra Life Expectancy 3 h cycle

MASTER TL-D Xtra Life Expectancy 12 h cycle



MASTER TL-D Xtra Life Expectancy 24 h cycle

MASTER TL-D Xtra Lumen Maintenance 3 h, 12 h + 24 h cycle

