

TL-D LIFEMAX Super 80

TL-D 58W/865 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h
Light Technical	
Colour Code	865 [CCT of 6500K]
Lamp Luminous Flux (Nom)	4800 lm
Colour Designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	96 %
Lumen maintenance 5,000 hours (nom.)	94 %
Colour Temperature, horizontal (Nom)	6500 K
Lamp Luminous Efficacy EM (Nom)	82 lm/W
Colour Rendering Index,horiz (Nom)	80
Operating and Electrical	
Technical Lamp Power (Nom)	58.5 W
Lamp current (nom.)	0.670 A
Voltage (nom.)	111 V

Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	Green Cap
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg
Product Data	
Full product code	871150028496940
Order product name	TL-D 58W/865 1SL/25
EAN/UPC – product	8711500284969
Order code	927983286536
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927983286536
Net weight (piece)	0.230 kg

TL-D LIFEMAX Super 80



Dimensional drawing





TL-D 58W/865/GC

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/865 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

Photometric data



Lifetime



TL-D LIFEMAX Super 80

Lifetime

