



MASTER TL-D Xtra

MASTER TL-D Xtra 58W/865 SLV

This TL-D Xtra lamp offers a longer lifetime and guarantees fewer early failures. This results in low maintenance costs and saves on expensive spot replacement. It is therefore suitable for places where lamp replacement is expensive due to high ceilings or disturbance of operations. This lamp can be operated on existing gear or dedicated HF Xtreme gear.

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	0.665 A	
Life to 50% Failures (Nom)	36,000 hour(s)	Controls and Dimming	
Light Technical		Dimmable	
Color Code	865 [CCT of 6500K]	Yes	
Luminous Flux	5,000 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Bulb Shape	
Correlated Color Temperature (Nom)	6500 K	T8 [26 mm (T8)]	
Luminous Efficacy (rated) (Nom)	86 lm/W	Approval and Application	
Color rendering index (CRI)	>80	Mercury (Hg) Content (Nom)	
Operating and Electrical		Energy Consumption kWh/1000 h	
Power Consumption	58 W	Product Data	
		Order product name	
		MASTER TL-D Xtra 58W/865 SLV	

MASTER TL-D Xtra

Full product name	MASTER TL-D Xtra 58W/865 SLV
Full product code	871150089285040
Order code	927983486514
Material Nr. (12NC)	927983486514
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500892850
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500892867

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 58W/865 SLV	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtra 58W/865 SLV

Lifetime




Life Expectancy Diagram - MASTER TL-D Xtra 58W/865 SLV



Life Expectancy Diagram - MASTER TL-D Xtra 58W/865 SLV

MASTER TL-D Xtra

Lifetime



Life Expectancy Diagram - MASTER TL-D Xtra 58W/865 SLV



Lumen Maintenance Diagram - MASTER TL-D Xtra 58W/865 SLV

