



MASTER TL5 High Output Eco

MASTER TL5 HO Eco 20=24W/830 UNP/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HO Eco lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	na [Not Applicable]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	1950 lm
Luminous Flux (Rated) (Nom)	1650 lm
Color Designation	Warm White (WW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	99 lm/W
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	19.5 W
Lamp Current (Nom)	0.300 A

Temperature	
Design Temperature (Nom)	35 °C

MASTER TL5 High Output Eco


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Full product code	872790088084700
Order product name	MASTER TL5 HO Eco 20=24W/830 UNP/40

EAN/UPC - Product	8711500881304
Order code	927989983031
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927989983031
Net Weight (Piece)	52.000 g
ILCOS Code	FDH-20/30/1B-L/P-G5-16/550

Warnings and Safety

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Eco 20=24W/830 UNP/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

TL5 HO Eco 20=24W/830

Photometric data




Lightcolor /830




Lightcolor /830

MASTER TL5 High Output Eco


Lifetime



MASTER TL5 HO Eco Life Expectancy 3 h cycle



MASTER TL5 HO Eco Life Expectancy 12 h cycle



MASTER TL5 HO Eco Lumen Maintenance 3 h + 12 h cycle

