

# T5 Standard

## F14T5/830/ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	G5
Features	HE Alto® [High Efficiency Alto]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,350 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	14.0 W
Lamp Current (Nom)	0.165 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	14W/830 Min Bipin T5 HE ALTO UNP/40
Full product name	F14T5/830/ALTO 40PK
Order code	230771
Material Nr. (12NC)	927990483022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677230777
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677230772


T5 Standard

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
14W/830 Min Bipin T5	11/16 inch	21-5/8 inch	21-15/16 inch	21-13/16 inch	22-3/16 inch
HE ALTO UNP/40					

Photometric data




Spectral Power Distribution Colour - 14W/830 Min Bipin T5 HE ALTO UNP/40

Lifetime




Life Expectancy Diagram - 14W/830 Min Bipin T5 HE ALTO UNP/40



Life Expectancy Diagram - 14W/830 Min Bipin T5 HE ALTO UNP/40

T5 Standard

Lifetime



Lumen Maintenance Diagram - 14W/830 Min Bipin T5 HE ALTO UNP/40

