



# T5 Standard

## F28T5/835 ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

### Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	24000 h
Features	HE Alto® [ High Efficiency Alto]
System Description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Light Technical	
Color Code	835 [ CCT of 3500K]
Initial lumen (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2675 lm
Color Designation	White (WH)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80

Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	27.9 W
Lamp Current (Nom)	0.170 A

Temperature	
Design Temperature (Nom)	35 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap-Base Information	Green [ Green Cap]

# T5 Standard

## Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg

## Product Data

Order product name	28W/835 Min Bipin T5 HE ALTO UNP/40
EAN/UPC - Product	046677230852

Order code	230854
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927990683522
Net Weight (Piece)	104.500 g
ILCOS Code	FDH-28/35/1B-L/P-G5-16/1150


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
28W/835 Min Bipin T5	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm
HE ALTO UNP/40					

## TL5 HE F28T5/835 HE Alto

## Photometric data



LDPB\_TL5-HE8\_835-Spectral power distribution B/W



LDPO\_TL5-HE8\_835-Spectral power distribution Colour

# T5 Standard

## Lifetime



LDLE\_TL5-HE8\_0001-Life expectancy diagram

LDLE\_TL5-HE8\_0002-Life expectancy diagram



LDLM\_TL5-HE8\_0001-Lumen maintenance diagram

