



MASTER TL5 High Efficiency Eco

MASTER TL5 HE Eco 25=28W/840 UNP/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HE Eco lamp offers excellent lumen maintenance and colour rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information	
Cap base	G5 [G5]
Life to 50% failures preheat (nom.)	25000 h
Features	na [Not Applicable]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %
Light Technical	
Colour code	840 [CCT of 4,000 K]
Luminous flux (nom.)	2900 lm
Luminous flux (rated) (nom.)	2600 lm
Colour designation	Cool White (CW)
Luminous efficacy (@ max. lumen, rated) (nom.)	114 lm/W
Correlated colour temperature (nom.)	4000 K
Luminous efficacy (rated) (nom.)	103 lm/W
Color rendering index (max.)	85

Color rendering index (min.)	80
Color rendering index (nom.)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Rated) (Nom)	25.2 W
Lamp current (nom.)	0.170 A

Temperature

Design temperature (nom.)	35 °C
---------------------------	-------

Controls and Dimming

Dimmable	yes
----------	-----

MASTER TL5 High Efficiency Eco

Approval and Application

Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	28 kWh

Product Data


Full product code	872790082589300
Order product name	MASTER TL5 HE Eco 25=28W/840 UNP/40
EAN/UPC – product	8711500880017

Order code	82589300
Local Code	25840TL5ECO
Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927990984031
Net weight (piece)	105.800 g
ILCOS Code	FDH-25/40/1B-L/P-G5-16/1150

Warnings and Safety

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL5 HE Eco 25=28W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco 25=28W/840 UNP/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

Photometric data



Lightcolour /840



Lightcolour /840

MASTER TL5 High Efficiency Eco

Lifetime

