

PHILIPS

Lighting



# MASTER TL5 High Efficiency Eco 高效率省電日光燈管

## MASTER TL5 HE Eco 25=28W/840 1SL/40

直徑 16 mm 的螢光燈管

### 产品数据

基本資訊	
接口	G5 [ G5]
至 50% 故障預熱的使用時間 (標稱)	25000 h
功能	na [ Not Applicable]
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	99 %
額定 LSF (預熱 8000 小時), 3 小時	99 %
額定 LSF (8000 小時), 3 小時	99 %
額定 LSF (預熱 16000 小時), 3 小時	99 %
額定 LSF (預熱 2000 小時), 3 小時	94 %

照明科技	
色碼	840 [ CCT of 4000K (841)]
光通量 (標稱)	2900 lm
光通量 (額定) (標稱)	2600 lm
色彩名稱	冷白色 (CW)
光效 (於最大流明, 額定) (標稱)	114 lm/W
相關色溫 (標稱)	4000 K
光效 (額定) (標稱)	103 lm/W
演色性指數 (最大)	85
演色性指數 (最小)	80

演色性指數 (標稱)	82
額定 SLMF (2000 小時)	96 %
額定 SLMF (4000 小時)	95 %
額定 SLMF (6000 小時)	94 %
額定 SLMF (8000 小時)	93 %
額定 SLMF (12000 小時)	92 %
額定 SLMF (16000 小時)	91 %
額定 SLMF (20000 小時)	90 %

運作和電氣	
Power (Rated) (Nom)	25.2 W
燈具電流 (標稱)	0.170 A

溫度	
設計溫度 (標稱)	35 °C

控制調光	
可調光	Yes

應用	
能源效益標籤 (EEL)	A+

## MASTER TL5 High Efficiency Eco 高效率省電日光燈管


汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	28 kWh
<b>產品參數</b>	
完整產品碼	872790090820601
訂購產品名稱	MASTER TL5 HE Eco 25=28W/840 1SL/40
EAN/UPC - 產品	8727900908206
訂購代碼	927990984033

分子 - 各件數量	1
分子 - 每一外盒內件數	40
材質編號(12NC)	927990984033
淨重 (件)	96.600 g
ILCOS Code	FDH-25/40/1B-L/P-G5-16/1150

### 安全提示

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



### 二维绘图



TL5 HE Eco 25=28W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco 25=28W/840 1SL/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

### 光度数据



# MASTER TL5 High Efficiency Eco 高效率省電日光燈管

## 壽命

