



MASTER TL5 High Output 90 De Luxe



MASTER TL5 HO 90 De Luxe 49W/952 1SL/20

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5 [G5]
Flux measurement reference	Sphere
Light Technical	
Color Code	950 [CCT of 5000K]
Luminous Flux	3,800 lm
Color Designation	Daylight
Chromaticity Coordinate X (Nom)	0.34
Chromaticity Coordinate Y (Nom)	0.351
Correlated Color Temperature (Nom)	5200 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color rendering index (CRI)	92
Operating and Electrical	
Power Consumption	49.8 W
Lamp Current (Nom)	0.255 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	50 kWh
EPREL Registration Number	423474
Product Data	
Order product name	MASTER TL5 HO 90 De Luxe 49W/952 1SL20
Full product name	MASTER TL5 HO 90 De Luxe 49W/952 1SL/20
Full product code	871150089062700
Order code	89062700
Material Nr. (12NC)	927991595024
Numerator - Quantity Per Pack	1

MASTER TL5 High Output 90 De Luxe


EAN/UPC - Product/Case	8711500890627
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900895216

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 49W/952 1SL20	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 90 De Luxe 49W/952 1SL20

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 49W/952 1SL20



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 49W/952 1SL20

MASTER TL5 High Output 90 De Luxe

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 90 De Luxe 49W/952
1SL20

