



MASTER TL-D Power Saver Set

MASTER TL-D Power Saver Set 12=18W/840 1SL/25

The MASTER TL-D Power Saver Set is a perfect solution for upgrading your existing lighting installation with a special TL-D lamp with an intelligent starter. It offers considerable energy savings while maintaining the same lighting level and a better light quality. The MASTER TL-D Power Saver Set is easy to install, simply by changing the lamp and the starter. The benefits are huge in all current installations with TL-D lamps.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Mechanical and Housing	
Cap base	G13 [Medium Bi-Pin Fluorescent]	Bulb shape	T8 [26 mm (T8)]
Light Technical		Approval and Application	
Colour Code	840 [CCT of 4000K]	Mercury (Hg) content (nom.)	2.0 mg
Colour designation	Cool White (CW)	Energy consumption kWh/1,000 hours	15 kWh
Correlated Colour Temperature	4000 K	Product Data	
Colour rendering index (CRI)	82	Order product name	MST TL-D Power Sav Set 12=18W/840 1SL/25
Controls and Dimming		Full product name	MASTER TL-D Power Saver Set 12=18W/840 1SL/25
Dimmable	No	Full EOC	872790091498600

MASTER TL-D Power Saver Set

Order code	91498600
Material no. (12 NC)	927997084002
Local order code	18840TLDPSS1X1
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900914986


Numerator – packs per outer box	25
EAN/UPC – Case	8727900914993

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Power Sav Set 12=18W/840 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data



Spectral Power Distribution Colour - MST TL-D Power Sav Set 12=18W/840 1SL/25

