



# MASTER TL-D Power Saver Set

## MST TL-D Power Sav Set 23=36W/840 1SL/25

The MASTER TL-D Power Saver Set is a perfect solution for upgrading your existing lighting installation with a special TL-D lamp with an intelligent starter. It offers considerable energy savings while maintaining the same lighting level and a better light quality. The MASTER TL-D Power Saver Set is easy to install, simply by changing the lamp and the starter. The benefits are huge in all current installations with TL-D lamps.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T8 [26 mm (T8)]
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	2.0 mg
Color rendering index (CRI)	82	Energy Consumption kWh/1000 h	28 kWh

MASTER TL-D Power Saver Set

Product Data	
Order product name	MST TL-D Power Sav Set 23=36W/840 1SL/25
Full product name	MST TL-D Power Sav Set 23=36W/840 1SL/25
Full product code	872790091504400
Order code	927997184002
Material Nr. (12NC)	927997184002

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900915044
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900915051

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Power Sav Set 23=36W/840 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - MST TL-D Power Sav Set 23=36W/840 1SL/25

