



# Actinic BL TL(-K) / TL-D(-K)

## Actinic BL TL MINI 4W/10

Tubular low-pressure mercury vapour fluorescent lamps

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
UV Depreciation at 1000 h	25 %
UV Depreciation at 2000 h	35 %
UV Depreciation at 5000 h	17 %
Operating and Electrical	
Power Consumption	4.5 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	29 V
Voltage (Nom)	29 V
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]

Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	Actinic BL TL MINI 4W/10
Full product name	Actinic BL TL MINI 4W/10
Full product code	871150095142727
Order code	928000001030
Material Nr. (12NC)	928000001030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500951427
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500951441


# Actinic BL TL(-K) / TL-D(-K)

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 4W/10	16 mm	135.9 mm	143 mm	140.6 mm	150.1 mm

## Photometric data



Spectral Power Distribution Colour – Actinic BL TL MINI 4W/10

