



TUV TL Mini

TUV 4W FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

产品数据

一般資訊	
燈座基底	G5 [G5]
可用使用始間 (標稱)	6,000 h
照明技術	
色碼	TUV
色彩名稱	- [未指定]
使用壽命期間的折舊	25 %
運轉與電力	
耗電量	4.5 W
燈具電流 (標稱)	0.17 A
電壓 (標稱)	29 V


電壓 (標稱)	29 V
機械與外罩	
燈泡形狀	T16 [T 16mm]
認證與應用	
汞 (Hg) 含量 (標稱)	4.4 mg
UV	
UV-C 輻射 (100 小時)	0.9 W
產品資料	
下訂產品名稱	TUV 4W FAM/10X25BOX
完整產品名稱	TUV 4W FAM/10X25BOX

TUV TL Mini

完整產品代碼	871150063872427
訂單代碼	928000104013
材質 Nr. (12NC)	928000104013
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500638724


分子 - 每一外盒包裝	250
EAN/UPC - 箱	8711500638748

二维绘图



Product	D	C
TUV 4W FAM/10X25BOX	16 mm	150.1 mm

光度数据



Spectral Power Distribution Colour - TUV 4W FAM/10X25BOX

