



TUV TL Mini

TUV4T5 4W 25PK

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	G5 [G5]
Main Application	Disinfection
Useful Life (Nom)	6000 h
System Description	na [-]
Light technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	0.25 %

Operating and electrical	
Power (Rated) (Nom)	4.5 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	29 V
Mechanical and housing	
Cap-Base Information	2 Pins (2P)
Bulb Shape	T5 [T5]

TUV TL Mini

Approval and application

Mercury (Hg) Content (Nom) 4.4 mg

UV

UV-C Radiation at 100 hr 0.9 W

Product data

Order product name TUV 4W FAM/10X25BOX

EAN/UPC - Product 8711500638724


Order code 363713

Numerator - Quantity Per Pack 1


Numerator - Packs per outer box 250

Material Nr. (12NC) 928000104013

Net Weight (Piece) 18.600 g




Dimensional drawing



TUV 4W FAM/10X25BOX

Product	D	C
TUV 4W FAM/10X25BOX	16 mm	150.1 mm

Photometric data



XDPB_XUTUV-Spectral power distribution B/W

XDPO_XUTUV-Spectral power distribution Colour

