

T5 Preheat

F6T5/CW FAM/25

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.


Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	260 lumen
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	43 lm/W
Color rendering index (CRI)	60
Operating and Electrical	
Power Consumption	6.0 W
Lamp Current (Nom)	0.160 A
Voltage (Nom)	42 V
Voltage (Nom)	42 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	F6T5/CW FAM/25
Order code	928000503321
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928000503321
Full product name	F6T5/CW FAM/25
EAN/UPC - Case	50046677114638
EAN/UPC - Product/Case	046677114633


T5 Preheat

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F6T5/CW FAM/25	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - F6T5/CW FAM/25

