

TL Mini consumer products

TL Mini 8W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	10,000 h
Light Technical	
Color Code	33-640
Luminous Flux	380 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	51 lm/W
Color rendering index (CRI)	59
Operating and Electrical	
Power Consumption	7.1 W
Lamp Current (Nom)	0.145 A

Voltage (Nom)	56 V
Voltage (Nom)	56 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	423490
Product Data	
Order product name	TL Mini 8W/33-640 1PP/10


TL Mini consumer products

Full product name	TL Mini 8W/33-640 1PP/10
Full product code	871150062695025
Local code description	TL8W33
Order code	928001003313
Material Nr. (12NC)	928001003313
Local order code	TL8W33


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500626950
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500262080

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/33-640 1PP/10	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm



Photometric data



Spectral Power Distribution Colour - TL Mini 8W/33-640 1PP/10

