



TL Mini Standard Colours

TL Mini 8W/54-765 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

General Information	
Cap-Base	G5 [G5]
Life To 10% Failures (Nom)	5000 h
Life to 50% Failures (Nom)	10000 h
Life to 50% Failures Preheat (Nom)	10000 h
System Description	na [-]

Light Technical	
Colour Code	54-765
Luminous Flux (Nom)	340 lm
Colour Designation	Cool Daylight
Lumen Maintenance 10000 h (Nom)	58 %
Lumen Maintenance 2000 h (Nom)	80 %
Lumen Maintenance 5000 h (Nom)	70 %
Colour Temperature, horizontal (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	48 lm/W
Colour Rendering Index horiz (Nom)	75

Operating and Electrical	
Power (Rated) (Nom)	7.1 W
Lamp Current (Nom)	0.145 A
Voltage (Nom)	56 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label	A
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh


Product Data	
Full product code	871150071628627
Order product name	TL Mini 8W/54-765 FAM/10X25BOX
EAN/UPC - Product	8711500716286
Order code	71628627
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	250
Material Nr. (12NC)	928001005440
Net Weight (Piece)	27.000 g
ILCOS Code	FD-8/62/2A-E-G5

TL Mini Standard Colours

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

TL Mini 8W/54-765

Photometric data



Lightcolour /54-765



Lightcolour /54-765

