



# MASTER TL Mini Super 80 迷你日光燈管

## MASTER TL Mini Super 80 8W/830 FAM/10X25BOX

直徑 16 mm 的螢光燈管

### 产品数据

基本資訊	
接口	G5 [ G5]
至 10% 故障的使用時間 (標稱)	5000 h
至 50% 故障的使用時間 (標稱)	10000 h
至 50% 故障預熱的使用時間 (標稱)	10000 h
照明科技	
色碼	830 [ CCT of 3000K]
光通量 (標稱)	470 lm
色彩名稱	暖白色 (WW)
流明維護量 10000 h (標稱)	71 %
流明維護量 2000 h (標稱)	85 %
流明維護量 5000 h (標稱)	77 %
相關色溫 (標稱)	3000 K
光效 (額定) (標稱)	59 lm/W
演色性指數 (標稱)	85
運作和電氣	
Power (Rated) (Nom)	7.1 W
燈具電流 (標稱)	0.145 A
電壓 (標稱)	56 V


控制調光	
可調光	Yes
應用	
能源效益標籤 (EEL)	A
汞 (Hg) 含量 (標稱)	3.0 mg
能源消耗 kWh/1000 h	8 kWh
產品參數	
完整產品碼	871150071638527
訂購產品名稱	MASTER TL Mini Super 80 8W/830 FAM/10X25BOX
EAN/UPC - 產品	8711500716385
訂購代碼	928001008350
分子 - 各件數量	1
分子 - 每一外盒內件數	250
材質編號(12NC)	928001008350
淨重 (件)	27.000 g
ILCOS Code	FD-8/30/1B-E-G5

# MASTER TL Mini Super 80 迷你日光燈管

## 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## 二维绘图



TL 8W/830

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL Mini Super 80 8W/830 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

## 光度数据

