



MASTER TL Mini Super 80 迷你日光燈管

MST TL Mini 8W/840 FAM/10X25BOX

直徑 16 mm 的螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G5
通量測量參考	Sphere
壽命 (故障率 50 %) (標稱)	10,000 h

照明技術	
色碼	840 [CCT of 4000K]
光通量	450 lm
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	0.38
色度坐標 Y (Nom)	0.38
相關色彩溫度 (規範)	4000 K
光效 (額定) (標準)	59 lm/W
演色性指數 (CRI)	82

運轉與電力	
耗電量	7.1 W
燈具電流 (標稱)	0.145 A
電壓 (標稱)	56 V

電壓 (標稱)	56 V
---------	------

控制與調光	
可調光	是

機械與外罩	
燈泡形狀	T5 [16 mm (T5)]

認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	2.5 mg
汞 (Hg) 含量 (標稱)	3.0 mg
能源消耗 kWh/1000 h	8 kWh
EPREL 註冊碼	423496


產品資料	
下訂產品名稱	MST TL Mini 8W/840 FAM/10X25BOX
完整產品名稱	MST TL Mini 8W/840 FAM/10X25BOX
完整產品代碼	871150071642227

MASTER TL Mini Super 80 迷你日光燈管

訂單代碼	928001008450
材質 Nr. (12NC)	928001008450
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500716422


分子 - 每一外盒包裝	250
EAN/UPC - 箱	8711500716446

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL Mini 8W/840 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

光度数据



Spectral Power Distribution Colour - MST TL Mini 8W/840 FAM/10X25BOX

