



# TL Mini Blacklight Blue

## TL 8W BLB 1FM/10X25CC

This TL Miniature lamp (tube diameter 16 mm) is made of blacklight blue (dark blue) glass, which transmits UV-A radiation, but gives only a minimum of visible light. It is a perfect solution for quick detection of UV-reflecting materials. It is used especially for testing, inspection and analysis in various branches of industry, e.g. criminology, philately and medicine. Furthermore, it is applied to create special effects in the entertainment industry, e.g. in nightclubs and theaters.

### Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Mechanical and Housing	
Cap-Base	G5 [G5]	Bulb Shape	T5 [16 mm (T5)]
Life to 50% Failures (Nom)	10,000 hour(s)		
Light Technical		Product Data	
Color Code	108 [08 lead free glass]	Order product name	TL 8W BLB 1FM/10X25CC
Color Designation	Blacklight Blue	Full product name	TL 8W BLB 1FM/10X25CC
		Full product code	871150095104527
Operating and Electrical		Order code	95104527
Power Consumption	7.1 W	Material Nr. (12NC)	928001010803
Lamp Current (Nom)	0.145 A	Numerator - Quantity Per Pack	1
Voltage (Nom)	56 V	EAN/UPC - Product/Case	8711500951045
Voltage (Nom)	56 V	Numerator - Packs per outer box	250
		EAN/UPC - Case	8711500951038


## TL Mini Blacklight Blue

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 8W BLB 1FM/10X25CC	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

### Photometric data



Spectral Power Distribution Colour - TL 8W BLB 1FM/10X25CC

