



TL Mini Blacklight Blue

TL 8W BLB 1FM/10X25CC

This TL Miniature lamp (tube diameter 16 mm) is made of blacklight blue (dark blue) glass, which transmits UV-A radiation, but gives only a minimum of visible light. It is a perfect solution for quick detection of UV-reflecting materials. It is used especially for testing, inspection and analysis in various branches of industry, e.g. criminology, philately and medicine. Furthermore, it is applied to create special effects in the entertainment industry, e.g. in nightclubs and theaters.

Product data


General Information		UV	
Cap-Base	G5 [G5]	UV-B/UV-A (IEC)	0.25 %
Life to 50% Failures (Nom)	10000 h		
Light Technical		Product Data	
Colour Code	108 [08 lead free glass]	Full product code	871150095104527
Colour Designation	Blacklight Blue	Order product name	TL 8W BLB 1FM/10X25CC
Depreciation 2000 hrs	20 %	EAN/UPC - Product	8711500951045
Depreciation 5000 hrs	30 %	Order code	95104527
Operating and Electrical		Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	7.1 W	Numerator - Packs per outer box	250
Lamp Current (Nom)	0.145 A	Material Nr. (12NC)	928001010803
Voltage (Nom)	56 V	Net Weight (Piece)	25.300 g

TL Mini Blacklight Blue

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL 8W/108

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 8W BLB 1FM/10X25CC	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

Photometric data



Lightcolor /108



Lightcolor /108

