



TUV TL Mini

TUV 8W FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

产品数据


一般信息		电压 (标称)		56 V
底盖	G5 [G5]	机械和外壳		
有效寿命 (标称)	9,000 小时	灯泡外形	T16 [T 16 毫米]	
灯技术		审批和申请		
颜色代码	TUV	汞 (Hg) 含量 (标称)	4.4 mg	
颜色名称	- [未指定]	UV		
有效寿命下的衰减	15 %	100 小时下的紫外线 C 辐射	2.5 W	
操作和电气		产品数据		
功耗	7.1 W	订单产品名称	TUV 8W FAM/10X25BOX	
灯具电流 (标称)	0.145 A	完整的产品名称	TUV 8W FAM/10X25BOX	
电压 (标称)	56 V			

TUV TL Mini

完整产品代码	871150062368327
订购代码	928001104013
材料编号 (12NC)	928001104013
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500623683


计算器 - 每个外包装箱中的包数	250
EAN/UPC - 案例	8711500623706

二维绘图



Product	D	C
TUV 8W FAM/10X25BOX	16 mm	302.5 mm

光度数据



Spectral Power Distribution Colour - TUV 8W FAM/10X25BOX

