



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL MINI 15W/09 /10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

产品数据

基本資訊	
接口	G5 [G5]
可用使用時間 (最大)	1000 h

照明科技	
色碼	09
色彩名稱	Actinic
500 小時後的流明衰減	30 %
1000 小時後的流明衰減	40 %

運作和電氣	
Power (Rated) (Nom)	13 W
燈具電流 (標稱)	0.35 A
電壓 (標稱)	46 V

紫外線	
UV-A 輻射 100Hr (IEC)	2 W


產品參數	
完整產品碼	871150086677627
訂購產品名稱	Actinic BL TL MINI 15W/09 /10X25CC
EAN/UPC - 產品	8711500866776
訂購代碼	928001200911
分子 - 各件數量	1
分子 - 每一外盒內件數	250
材質編號(12NC)	928001200911
淨重 (件)	29.000 g

Actinic BL TL(-K)/TL-D(-K)

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 15W/09 /10X25CC	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

TL' 15W/09

